



Bringing Test Innovation to you

Datasheet

This product datasheet has been provided by John Godrich & SJ Electronics in Partnership with BINDER



Best conditions for your success

www.johngodrich.co.uk

www.sjelectronics.co.uk



Model KB 53 | Cooling incubators with compressor technology

The powerful virtuoso in cooling incubators for microorganisms: the KB masters temperature ranges from -5 °C to 100 °C. The new KB series consumes up to 30% less energy compared to its predecessor. With its extensive programming options and homogenous incubation conditions even when fully loaded, this cooling incubator covers a wide range of applications.

BENEFITS

- · Safe, reproducible incubation, even at high ambient temperatures
- Disinfection routine at 100 °C
- · Up to 30% lower energy consumption compared to the previous model



Model 53

MAIN FEATURES

- Temperature range: -5 °C to 100 °C
- APT.line[™] preheating chamber technology
- Up to 30% lower energy consumption compared to the previous model
- Cooling with compressor cooling unit
- Adjustable fan speed
- · Controller with time-segment and real-time programming



Model 53

- Inner door made of tempered safety glass
- 2 stainless steel racks
- Stackable
- Class 3.1 independent temperature safety device (DIN 12880) with visual and acoustic alarm
- Computer interface: Ethernet

ORDERING INFORMATION

Interior volume [cu.ft.]	Voltage	Option model	Version	ArtNo.
Model KB 53				
1.9	230 V 1 ph 50 Hz	Standard	KB053-230V	9020-0199
	120 V 1 ph 60 Hz	Standard	KB053UL-120V	9020-0302



TECHNICAL DATA

Article Number Performance Data Temperature Temperature range [°C] Temperature variation at 37 °C [± K] Temperature fluctuation at 37 °C [± K]	9020-0199 -5100 0.2 0.1 5 2	9020-0302 -5100 0.2 0.1 5
Temperature range [°C] Temperature variation at 37 °C [± K]	0.2 0.1 5	0.2 0.1
Temperature variation at 37 °C [± K]	0.2 0.1 5	0.2 0.1
	0.1 5	0.1
Temperature fluctuation at 37 °C [± K]	5	
		E
Heating-up time to 37 °C [min]	2	5
Recovery time after 30 seconds door open at 37 °C [min]	-	2
Electrical data		
Rated Voltage [V]	230	120
Power frequency [Hz]	50	60
Nominal power [kW]	0.6	0.6
Unit fuse [A]	10	12.5
Phase (Nominal voltage) [ph]	1	1
Outer dimensions		
Width net [mm]	635	635
Height net [mm]	835	835
Depth net [mm]	580	580
Wall clearance back [mm]	100	100
Wall clearance sidewise [mm]	100	160
Doors		
Inner doors	1	1
Unit doors	1	1
Internal Dimensions		
Width [mm]	400	400
Height [mm]	400	400
Depth [mm]	330	330
Measures		
Interior volume [L]	53	53
Net weight of the unit (empty) [kg]	78	78
permitted load [kg]	40	40
Load per rack [kg]	15	15
Environment-specific data		
Energy consumption at 37 °C [Wh/h]	70	70
Sound-pressure level [dB(A)]	49	49
Fixtures		
Number of shelves (std./max.)	2/4	2/4

1 All technical data is specified for unloaded units with standard equipment at an ambient temperature of +22 °C ±3 °C and a power supply voltage fluctuation of ±10 %. The temperature data is determined in accordance to BINDER factory standard following DIN 12880, observing the recommended wall clearances of 10 % of the height, width, and depth of the inner chamber. Technical data refers to 100 % fan speed. All indications are average values, typical for units produced in series. We reserve the right to change technical specifications at any time.



OPTIONS AND ACCESSORIES

Designation	Description	*	ArtNo.
	back		
	10 mm	01	8012-0395
	30 mm	01	8012-1292
	50 mm	01	8012-1294
	left	-	
	10 mm	01	8012-039
	30 mm	01	8012-115
Access port with silicone	 right		
lug	- 10 mm	01	8012-039
	30 mm	01	8012-115
	top		
	10 mm	01	8012-039
	30 mm	01	8012-115
	50 mm	01	8012-116
	100 mm	01, 10	8012-116
larm output, zero- oltage	for temperature (±2 °C), accessible via 6-pin DIN socket (max. 24 V - 2.5 A), with audible signal that can be switched off	-	8012-108
Analog output, 4 – 20			8012-043
nA	for temperature values (output not adjustable)	02	8012-107
Calibration certificate,	for temperature; for extending the measurement in center of chamber to include another test temperature	-	8012-112
· · · · · · · · · · · · · · · · · · ·	for temperature, measurement in center of chamber at specified temperature	_	8012-113
Calibration certificate,	temperature measurement incl. certificate and 27 measuring points at specified temperature	-	8012-159
emperature	temperature measurement incl. certificate, 15- 18 measuring points at specified temperature	-	8012-157
	temperature measurement incl. certificate, 9 measuring points at specified temperature	-	8012-155
Cart	Cart – stable cart, casters with locking brakes, dimensions: W 1,000 x D 800 x H 780 mm	_	9051-001
	with visual alarm (DIN 12880)		
Class 3.3 independent	120 V option model	_	8012-045
emperature safety	230 V option model		8012-045
levice		-	8012-108
Data Logger Kit	T 220: For continuous temperature logging from -90 °C to 220 °C. The kit includes 1 data logger, Pt 100 sensor with 2 m extension cable and 1 magnetic fixture for mounting to the BINDER unit	19	8012-071
Data Logger Software	LOG ANALYZE software kit, configuration and evaluation software for all BINDER Data Logger Kits (incl. USB data cable)	19	8012-082
			8012-125
Door lock	lockable door handle	-	8012-177
	RS 422 cable set and RS 232 / RS 422 interface converter for connection to 10-way plug distributor or for connection to a unit		
	120 V, 60 Hz option model	-	8012-055
	230 V, 50/60 Hz option model	-	8012-055
Interface converter	RS 422 cable set and RS 422 / Ethernet interface converter for connection to 10-way plug distributor or for connection to a unit		
	120 V, 60 Hz option model	_	8012-040
	230 V, 50/60 Hz option model	_	8012-038
nterface converter, JSB / RS422	RS 422 cable set and RS 422 / USB interface converter for connection to 10-way plug distributor or for connection to a unit (USB-powered converter)	-	8012-066
	with 15 W light bulb		
nterior lighting	120 V option model	_	8012-106
	230 V option model	02	8012-106
nterior socket	Waterproof, switched flush-mounting box (CA3GD) for nominal voltage in unit interior, with cover and corresponding plug (nominal voltage; max. 500 W; max. 90 °C; protection class IP67)	07	8012-107
H-neutral detergent	concentrated, for gentle remove of residual contaminants; 1 kg	_	1002-001
•			
Notes > See last page			

Data Sheet Model KB 53



Designation	Description	*	ArtNo.
Pt 100 temperature	additional flexible Pt 100, interior, with external connection incl. LEMO connector (3-pin)		8012-1177
sensor			8012-1078
Rack	stainless steel	-	6004-0007
Rack accessories	Rack accessories – fasteners (1 set of 4) for additional security of racks	-	8012-0531
RS 422 interface	in place of Ethernet, for communication software	-	8012-1076
	modular plug distributor for 10 RS 422 interfaces		8012-0295
RS 422 interface, cable (15 m)	RS 422 connection cable (15 m) between plug distributor and RS 422 interface	-	5023-0036
RS 422 interface, cable (50 m)	RS 422 extension cable (50 m) between interface converter and unit or RS 232 / RS 422 plug distributor	-	5023-0117
Rubber pads	set of 4 anti-slip feet, for safe stacking of unit	10	8012-0001
Shelf, perforated	stainless steel	-	6004-0029
Shelf, reinforced	positioned at bottom level, max. load 67 kg, with additional attachment for operation of shaking device, stirring device or roller bottle system	-	8012-0287
Software	APT-COM [™] communications software		
	version 2 to 3, GLP edition	19	9053-0016
	version 3, BASIC edition	19	9053-0014
	version 3, GLP edition	19	9053-0015
	version 3, STANDARD edition	19	9053-0013
	APT-COM [™] communications software, price: for free		
	version 3, GLP DEMO Edition	19	9053-0008

* Notes > See last page

SERVICES

Designation	Description	*	ArtNo.
Installation services			
Data Logger Kit installation service	unit function instructions for operation and programming of the controller	18	DL100500
Installation	and set up of unit at operating location, connect to existing connections	13, 18	DL100100
Preventive maintenance			
Preventive maintenance	Executive of equipment inspection according to maintenance plan	14, 18	DL200300
Calibration services			
Data Logger Kit calibration service	including certificate, one measuring point in center of chamber at specified temperature	14, 16, 17, 18	DL300101
Temperature measurement 18 measuring points	including certificate, 18 measuring points at specified temperature	14, 16, 17, 18	DL300118
Temperature measurement 27 measuring points	including certificate, 27 measuring points at specified temperature	14, 16, 17, 18	DL300127
Temperature measurement 9 measuring points	including certificate, 9 measuring points at specified temperature	14, 16, 17, 18	DL300109
Validation services			
Execution of IQ/OQ	in accordance with qualification folder	15, 18, 20	DL410200
Execution of IQ/OQ/PQ	in accordance with customer's requirement, price: on request	15, 18	DL440500
Qualification folder IQ/OQ	supporting documents for validation performed by customer, consisting of: IQ/OQ checklists, unit schematics, QM certificate in accordance with ISO 9001	15, 18, 20	8012-0873
Qualification folder IQ/OQ/PQ	supporting documents for validation performed by customer, in accordance with customer's requirement, extension of Qualification folder IQ/OQ by chapter PQ	15, 18	8012-096
Warranty service			
Extension of the warranty from 2 to 3 years	beginning with the date of delivery, wearing parts are not included	-	DL018047
Extension of the warranty from 2 to 5 years	beginning with the date of delivery, wearing parts are not included	-	DL018042

* Notes > See last page



NOTES

- Condensation may occur in the area around the access port. Access ports may be placed in custom locations for an additional charge. 01 02
- UL mark is not granted when this option is used. Heat resistant only to max. 200 °C.
- 03
- Only available on units rated for 230 V. 04
- 06 Heating-up time may increase as a result of the lower heat conductivity. 07 The additional heat input may affect the temperature behavior.
- Not in conjunction with the optional access port, door with window and interior lighting. 09
- 10 11 12 Not available on 23-liter units.
- Not available on 23- or 53-liter units.
- Only available on units rated for 230 V or 400 V.
- 13 Installation and connections take place at unit location; transport within the company only upon consultation.
- 14 We recommend a BINDER service contract (see the chapter on BINDER Service) to cover unit inspections, calibrations and validations
- 15 OQ according to Yellow Paper = completed factory validation documentation of all OQ checklists.
- Sensor calibration is performed in an accredited calibration laboratory. 16
- 17
- Calibration is performed according to the BINDER factory standard. Quoted prices do not include travel costs. Please refer to the chapter on BINDER Service for travel costs for your region. Quoted prices for services performed in Switzerland do not 18 include a country-specific added fee (available on request).
- For additional accessories, refer to the Process documentation chapter. 19
- 20 When ordering IQ/OQ qualification folders and associated IQ/OQ execution on one order, we offer a 15 % discount for both items. When ordering IQ/OQ/PQ qualification folders and associated IQ/OQ/PQ execution on one order, we offer a 15 % discount for the item of the IQ/OQ/PQ folder.





Bringing Test Innovation to you

Datasheet

This product datasheet has been provided by John Godrich & SJ Electronics in Partnership with BINDER



Best conditions for your success

www.johngodrich.co.uk

www.sjelectronics.co.uk